

Space for Transmitters in Probe Assembly Heads

HEAD Model Number	TRANSMITTER SPACE		PROBES Typical
	Diameter, mm (in)	Height, mm (in)	
NB1	47.6 (1 7/8)	19.0 (3/4)	NB1-ICSS-14G-12 PR-12-2-100-1/8-6-E
NB2	31.7 (1 1/4)	19.0 (3/4)	NB2-ICSS-14G-24 PR-14-2-100-1/8-6-E
NB3	57.1 (2 1/4)	25.4 (1)	NB1-ICSS-14G-12 PR-18-2-100-1/8-6-E
NB4	22.2 (7/8)	9.5 (3/8)	NB4-ICSS-14G-12 PR-19-2-100-1/8-6-E
NEPA, NEPB	69.8 (2 3/4)	38.1 (1 1/2)	NEPB-ICSS-14G-12 NEPB-2-100-1/8-6-E
NBS	50.8 (2)	31.7 (1 1/4)	NBS-ICSS-14G-12 NBS-2-100-1/8-6-E
NSA, NSB, NSC	50.8 (2)	31.7 (1 1/4)	NSB-ICSS-14G-12 NSB-2-100-1/8-6-E
NBB	47.6 (1 7/8)	19.0 (3/4)	NBB-ICSS-14G-12 NBB-2-100-1/8-6-E
NBN	50.8 (2)	19.0 (3/4)	NBN-ICSS-14G-12 NBN-2-100-1/8-6-E
NBG	44.4 (1 3/4)	19.0 (3/4)	NBG-ICSS-14G-12 NBG-2-100-1/8-6-E
NXT	47.6 (1 7/8)	50.8 (2)	NXT-ICSS-14G-12 NXT-2-100-1/8-6-E
HEP-TX	76.2 (3)	50.8 (2)	HEP-TX-100-J1 HEP-TX-110-PT1
HEP-TX70	76.2 (3)	50.8 (2)	HEP-TX71-J-50-350C HEP-TX75-50-350C